

DN-FE2L12 Cut Sheet



DINnector screw circuit protection terminal block, accepts wire size 24-12 AWG, gray, 12 VAC/VDC LED indicator(s). Package of 50. 20A when used as a disconnect; 10A when used with a DN-SUPP-nn.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-FE2L12>

Technical Specifications

| | |
|---------------------|---|
| Brand | DINnector |
| Item | Terminal block |
| Connector Type | Screw |
| Terminal Block Type | Circuit protection |
| Wire Size | 24-12 AWG |
| Color | Gray |
| Voltage Rating | 12 VAC/VDC |
| Indicator | 12 VAC/VDC LED |
| Quantity per Pack | 50 |
| Application | 20A when used as a disconnect; 10A when used with a DN-SUPP-nn |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E179129 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DN-FE2L12.pdf>
See store item page for other formats.