

# DN-FE2L24-5 Cut Sheet



DINnector screw circuit protection terminal block, accepts wire size 24-12 AWG, gray, 24 VAC/VDC LED indicator(s). Package of 5. 20A when used as a disconnect; 10A when used with a DN-SUPP-nn.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-FE2L24-5>

## Technical Specifications

<b>Brand</b>	DINnector
<b>Item</b>	Terminal block
<b>Connector Type</b>	Screw
<b>Terminal Block Type</b>	Circuit protection
<b>Wire Size</b>	24-12 AWG
<b>Color</b>	Gray
<b>Voltage Rating</b>	24 VAC/VDC
<b>Indicator</b>	24 VAC/VDC LED
<b>Quantity per Pack</b>	5
<b>Application</b>	20A when used as a disconnect; 10A when used with a DN-SUPP-nn

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>