

# DN-FE2L24 Cut Sheet



DINnector screw circuit protection terminal block, accepts wire size 24-12 AWG, gray, 24 VAC/VDC LED indicator(s). Package of 50. 20A when used as a disconnect; 10A when used with a DN-SUPP-nn.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-FE2L24>

## Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Wire Size	24-12 AWG
Color	Gray
Voltage Rating	24 VAC/VDC
Indicator	24 VAC/VDC LED
Quantity per Pack	50
Application	20A when used as a disconnect; 10A when used with a DN-SUPP-nn

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DN-FE2L24.pdf>  
See store item page for other formats.