

DN-FE4L12 Cut Sheet



DINnector screw circuit protection terminal block, accepts wire size 24-10 AWG, gray, 12 VAC/VDC LED indicator(s). Package of 50. 25A when used as a disconnect; 10A when used with a DN-SUPP-nn.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-FE4L12>

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Wire Size	24-10 AWG
Color	Gray
Voltage Rating	12 VAC/VDC
Indicator	12 VAC/VDC LED
Quantity per Pack	50
Application	25A when used as a disconnect; 10A when used with a DN-SUPP-nn

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DN-FE4L12.pdf>
See store item page for other formats.