DN-G4MN Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



DINnector screw grounding terminal block, single-level, accepts wire size 14–4 AWG, yellow/green, 35mm DIN rail mount. Package of 8.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/DN-G4MN

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Grounding
Number of Levels	1
Number of Inputs	1
Number of Outputs	1

Wire Size	14–4 AWG
Color	Yellow/green
Mounting	35mm DIN rail
SCCR Rating	10 kA SCCR
Quantity per Pack	8
Application	Use to mechanically and electrically connect wires to 35mm DIN rail through the clamping foot

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/DN-G4MN.pdf
See store item page for other formats.