

# DN-MG10 Cut Sheet



DINnector screw mini grounding terminal block, accepts wire size 24-10 AWG, green and yellow, 15mm DIN rail mount, 10kA SCCR. Package of 20. Use to mechanically and electrically connect wires to 15mm DIN rail through the screw-down clamping foot.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-MG10>

## Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Mini grounding
Wire Size	24-10 AWG
Color	Green and yellow
Mounting	15mm DIN rail
SCCR Rating	10kA SCCR
Quantity per Pack	20
Application	Use to mechanically and electrically connect wires to 15mm DIN rail through the screw-down clamping foot

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DN-MG10.pdf>  
See store item page for other formats.