DN-Q10-A Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

DINnector spring clamp feedthrough terminal block, single-level, accepts wire size 24–10 AWG, gray, 30A, 600V rated (UL), 35mm DIN rail mount. Package of 50.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/DN-Q10-A

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Spring clamp
Terminal Block Type	Feedthrough
Number of Levels	1
Number of Inputs	1
Number of Outputs	1
Wire Size	24–10 AWG

Color	Gray
Amperage Rating	30A
Voltage Rating	600V rated (UL)
Mounting	35mm DIN rail
SCCR Rating	10 kA SCCR
Quantity per Pack	50
For Use With	Jumpers DN-24J4Y, DN-2J4Y and DN-3J4Y

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/DN-Q10-A.pdf
See store item page for other formats.