

DN-SUPP-4 Cut Sheet



DINnector mini supplementary protector, with reset, 4A, 250 VAC/75 VDC, blade connection, 1-pole, UL 1077 recognized. Package of 20. For use with DN-FE2 and DN-FE4 series socket.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-SUPP-4>

Technical Specifications

Brand	DINnector
Item	Mini supplementary protector
Reset	Yes
Amperage Rating	4A
Voltage Rating	250 VAC/75 VDC
Terminal Connection	Blade
Number of Poles	1
Quantity per Pack	20
For Use With	DN-FE2 and DN-FE4 series socket
UL Rating	UL 1077 recognized

Agency Approvals

UL Listed File #	None
UL Recognized File #	E320462
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DN-SUPP-4.pdf>
See store item page for other formats.