DN-T6 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



DINnector screw single-level feedthrough terminal block, accepts wire size 20-6 AWG, gray, 65A, 600V rated (UL), 35mm DIN rail mount. Package of 50.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/DN-T6

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Single-level feedthrough
Wire Size	20-6 AWG
Color	Gray
Amperage Rating	65A
Voltage Rating	600V rated (UL)
Mounting	35mm DIN rail
SCCR Rating	100kA SCCR
Quantity per Pack	50

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document