

DN-TL14S-A Cut Sheet



DINnector screw triple-level sensor terminal block, accepts wire size 26-14 AWG, gray, 10A, 35mm DIN rail mount, 10kA SCCR. Package of 25. For use with jumpers DN-12JL14B-A, DN-12JL14-A, DN-2JL14B-A, DN-2JL14-A, DN-3JL14B-A, and DN-3JL14-A.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-TL14S-A>

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Triple-level sensor
Wire Size	26-14 AWG
Color	Gray
Amperage Rating	10A
Voltage Rating	300V rated (UL)
Mounting	35mm DIN rail
SCCR Rating	10kA SCCR
Quantity per Pack	25
For Use With	Jumpers DN-12JL14B-A, DN-12JL14-A, DN-2JL14B-A, DN-2JL14-A, DN-3JL14B-A, and DN-3JL14-A

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document