

DNFK1AC120 Cut Sheet



Hammond rack fan, 100 CFM, 115 VAC operating voltage, 50/60 Hz.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DNFK1AC120>

Technical Specifications

Brand	Hammond
Item	Rack fan
Free Airflow	100 CFM
Operating Voltage	115 VAC
Hertz	50/60 Hz
Includes	(1) 72in NEMA 1-15P power cord, (2) chrome metal grilles and mounting hardware

Agency Approvals

UL Listed File #	E331157
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR43697
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DNFK1AC120.pdf>
See store item page for other formats.