

DPE18BL Cut Sheet



Schneider Electric Easy TeSys series IEC contactor, 18A, (3) N.O. power poles, (1) N.O. auxiliary contacts, 24 VDC coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPE18BL>

Technical Specifications

Brand	Schneider Electric
Item	Contactor
Series	Easy TeSys
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	18A
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O.
Coil Voltage	24 VDC
Horsepower Rating	7-1/2hp
SCCR Rating	5kA SCCR
UL Rating	UL 60947-4-1
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E164862
CE	View CE declarations
CSA File #	164581
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DPE18BL.pdf>
See store item page for other formats.