

# DPE18U7 Cut Sheet



Schneider Electric Easy TeSys series IEC contactor, 18A, (3) N.O. power poles, (1) N.O. auxiliary contacts, 240 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPE18U7>

## Technical Specifications

<b>Brand</b>	Schneider Electric
<b>Item</b>	Contactor
<b>Series</b>	Easy TeSys
<b>Contactor Type</b>	IEC
<b>Actuator Type</b>	Magnetic
<b>Amperage Rating</b>	18A
<b>Power Poles</b>	(3) N.O.
<b>Auxiliary Contacts</b>	(1) N.O.
<b>Coil Voltage</b>	240 VAC (50/60Hz)
<b>Horsepower Rating</b>	7-1/2hp
<b>SCCR Rating</b>	5kA SCCR
<b>UL Rating</b>	UL 60947-4-1
<b>Mounting</b>	35mm DIN rail or panel

## Agency Approvals

<b>UL Listed File #</b>	E164862
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	164581
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DPE18U7.pdf>  
See store item page for other formats.