

DPE25B7 Cut Sheet



Schneider Electric Easy TeSys series IEC contactor, 25A, (3) N.O. power poles, (1) N.O. auxiliary contacts, 24 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPE25B7>

Technical Specifications

Brand	Schneider Electric
Item	Contactors
Series	Easy TeSys
Contactors Type	IEC
Actuator Type	Magnetic
Amperage Rating	25A
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O.
Coil Voltage	24 VAC (50/60Hz)
Horsepower Rating	10hp
SCCR Rating	5kA SCCR
UL Rating	UL 60947-4-1
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E164862
CE	View CE declarations
CSA File #	164581
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DPE25B7.pdf>
See store item page for other formats.