

# DPER03 Cut Sheet



Schneider Electric Easy TeSys series thermal overload relay, 0.25-0.40A adjustable, bi-metallic, direct mount power connection(s). For use with Schneider Electric DPE09 to DPE38 contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPER03>

## Technical Specifications

|                                 |  |
|---------------------------------|--|
| <b>Brand</b>                    | Schneider Electric                           |
| <b>Item</b>                     | Relay  |
| <b>Series</b>                   | Easy TeSys                                   |
| <b>Relay Type</b>               | Thermal overload                             |
| <b>Full Load Amperage Range</b> | 0.25-0.40A adjustable                        |
| <b>Operation Type</b>           | Bi-metallic                                  |
| <b>Auxiliary Contacts</b>       | (1) N.O./ (1) N.C.                           |
| <b>Trip Class</b>               | Trip Class 10                                |
| <b>Phase Loss Sensitive</b>     | Yes  |
| <b>Ground Fault Protection</b>  | No   |
| <b>Connection</b>               | Direct mount power                           |
| <b>For Use With</b>             | Schneider Electric DPE09 to DPE38 contactors |

## Agency Approvals

|                         |  |
|-------------------------|--|
| <b>UL Listed File #</b> | E164353                                |
| <b>CE</b>               | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>       | 164581                                 |
| <b>RoHS Status</b>      | Yes (See CE Doc)                       |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DPER03.pdf>  
See store item page for other formats.