

DPER06 Cut Sheet



Schneider Electric Easy TeSys series thermal overload relay, 1-1.6A adjustable, bi-metallic, direct mount power connection(s). For use with Schneider Electric DPE09 to DPE38 contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPER06>

Technical Specifications

Brand	Schneider Electric
Item	Relay
Series	Easy TeSys
Relay Type	Thermal overload
Full Load Amperage Range	1-1.6A adjustable
Operation Type	Bi-metallic
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
Connection	Direct mount power
For Use With	Schneider Electric DPE09 to DPE38 contactors

Agency Approvals

UL Listed File #	E164353
CE	View CE declarations
CSA File #	164581
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DPER06.pdf>
See store item page for other formats.