

DPG1-200 Cut Sheet



ProSense digital pressure gauge, 0 to 200 psig, 0.5% of full scale accuracy, stainless steel wetted parts, 1/4in male NPT process connection, lower mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPG1-200>

Technical Specifications

| | |
|--------------------|--|
| Brand | ProSense |
| Item | Digital pressure gauge |
| Scale | 0 to 200 psig |
| Accuracy | 0.5% of full scale |
| Wetted Parts | Stainless steel |
| Process Connection | 1/4in male NPT |
| Mounting | Lower |
| Includes | Rubber boot and (2) AAA alkaline batteries |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPG1-200.pdf>
See store item page for other formats.