

# DPG1-3000 Cut Sheet



ProSense digital pressure gauge, 0 to 3000 psig, 0.5% of full scale accuracy, stainless steel wetted parts, 1/4in male NPT process connection, lower mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPG1-3000>

## Technical Specifications

Brand	ProSense
Item	Digital pressure gauge
Scale	0 to 3000 psig
Accuracy	0.5% of full scale
Wetted Parts	Stainless steel
Process Connection	1/4in male NPT
Mounting	Lower
Includes	Rubber boot and (2) AAA alkaline batteries

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DPG1-3000.pdf>  
See store item page for other formats.