

DPM1-A-A2R-L Cut Sheet



ProSense digital panel meter, panel mount, 1/32 DIN, 8mm 4-digit red LED, analog input, 0/4-20 mA, (2) 5A SPST relays output, 21 to 53 VAC/13.5 to 70 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM1-A-A2R-L>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/32 DIN
Display Type	8mm 4-digit red LED
Input Current Signal Range	+/-20mA
Input Voltage Signal Range	+/-60VDC +/-10VDC +/-100mVDC
Output	0/4-20 mA, (2) 5A SPST relays
Operating Voltage	21 to 53 VAC/13.5 to 70 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document