

DPM1-A-LP Cut Sheet



ProSense digital panel meter, panel mount, 1/32 DIN, 10mm 4-digit red LED, loop powered current input.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM1-A-LP>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/32 DIN
Display Type	10mm 4-digit red LED
Input	Loop powered current
Input Current Signal Range	4-20 mA

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM1-A-LP.pdf>
See store item page for other formats.