

DPM1-A-L Cut Sheet



ProSense digital panel meter, panel mount, 1/32 DIN, 10mm 4-digit red LED, analog input, 21-53 VAC/10.5-70 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM1-A-L>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/32 DIN
Display Type	10mm 4-digit red LED
Input	Analog
Input Current Signal Range	+/- 20 mA
Input Voltage Signal Range	<ul style="list-style-type: none">• +/- 100 mVDC• +/- 10 VDC• +/- 20 VDC• +/- 200 VDC
Operating Voltage	21-53 VAC/10.5-70 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM1-A-L.pdf>
See store item page for other formats.