

DPM1-P-A2R-H Cut Sheet



ProSense digital panel meter, 1/32 DIN, 8mm 4-digit red LED, pulse and frequency input, 0/4-20 mA and (2) 5A SPST relays output, 85 to 265 VAC/100 to 300 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM1-P-A2R-H>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/32 DIN
Display Type	8mm 4-digit red LED
Input Pulse/Frequency Signal Type	NPN, PNP, contact, encoder, magnetic pickup, NAMUR, AC voltage frequency
Output	0/4-20 mA and (2) 5A SPST relays
Operating Voltage	85 to 265 VAC/100 to 300 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document