

# DPM1-P-A2R-L Cut Sheet



ProSense digital panel meter, panel mount, 1/32 DIN, 8mm 4-digit red LED, pulse or frequency input, 0/4-20 mA or (2) 5A SPST relays output, 21 to 53 VAC/13.5 to 70 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM1-P-A2R-L>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Digital panel meter
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	1/32 DIN
<b>Display Type</b>	8mm 4-digit red LED
<b>Input Pulse/Frequency Signal Type</b>	NPN, PNP, contact, encoder, magnetic pickup, NAMUR, AC voltage frequency
<b>Output</b>	0/4-20 mA or (2) 5A SPST relays
<b>Operating Voltage</b>	21 to 53 VAC/13.5 to 70 VDC
<b>Loop Powered</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>