

DPM1-T-L Cut Sheet



ProSense digital panel meter, 1/32 DIN, 10mm 4-digit red LED, RTD or thermocouple input, 21 to 53 VAC/10.5 to 70 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM1-T-L>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/32 DIN
Display Type	10mm 4-digit red LED
Input Thermocouple Signal Type	J, K, T, N
Input RTD Signal Types	Pt100
Operating Voltage	21 to 53 VAC/10.5 to 70 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document