

# DPM2-AT-HL Cut Sheet



ProSense digital panel meter, 1/8 DIN, 14mm 4-digit red LED, analog, RTD, thermocouple or potentiometer input, 20 to 265 VAC/11 to 265 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM2-AT-HL>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Digital panel meter
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	1/8 DIN
<b>Display Type</b>	14mm 4-digit red LED
<b>Input Current Signal Range</b>	+/-20mA
<b>Input Voltage Signal Range</b>	+/-200VDC +/-10VDC
<b>Input Thermocouple Signal Type</b>	J, K, T, N
<b>Input RTD Signal Types</b>	Pt100 and Pt1000
<b>Input Potentiometer Signal Range</b>	100-100k Ohms
<b>Operating Voltage</b>	20 to 265 VAC/11 to 265 VDC
<b>Loop Powered</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>