

DPM2-AT-HL Cut Sheet



ProSense digital panel meter, panel mount, 1/8 DIN, 14mm 4-digit red LED, analog, RTD, thermocouple or potentiometer input, 20-265 VAC/11-265 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM2-AT-HL>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14mm 4-digit red LED
Input	Analog, RTD, thermocouple or potentiometer
Input Current Signal Range	+/- 20 mA
Input Voltage Signal Range	<ul style="list-style-type: none">+/- 10 VDC+/- 200 VDC

Input Thermocouple Signal Type	J, K, T, N
Input RTD Signal Types	Pt100 and Pt1000
Input Potentiometer Signal Range	100-100k ohm
Operating Voltage	20-265 VAC/11-265 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM2-AT-HL.pdf>
See store item page for other formats.