

DPM2-E-2R-HL Cut Sheet



ProSense digital panel meter, 1/8 DIN, 14mm 4-digit red LED, AC/DC current or voltage input, (2) 8A SPDT relays output, 20 to 265 VAC/11 to 265 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM2-E-2R-HL>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14mm 4-digit red LED
Input Current Signal Range	0-1A AC 0-5A AC shunt 0-60 mVAC shunt 0-100 mVAC +/-1A DC +/-5A DC shunt +/-60 mVDC shunt +/-100 mVDC
Input Voltage Signal Range	0-20 VAC 0-200 VAC 0-600 VAC +/-20 VDC +/-200VDC +/- 600 VDC
Output	(2) 8A SPDT relays
Operating Voltage	20 to 265 VAC/11 to 265 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document