

# DPM2-E-HL Cut Sheet



ProSense digital panel meter, 1/8 DIN, 14mm 4-digit red LED, AC/DC current or voltage input, 20 to 265 VAC/11 to 265 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM2-E-HL>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Digital panel meter
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	1/8 DIN
<b>Display Type</b>	14mm 4-digit red LED
<b>Input Current Signal Range</b>	0-1A AC 0-5A AC shunt 0-60 mVAC shunt 0-100 mVAC +/-1A DC +/-5A DC shunt +/-60 mVDC shunt +/-100 mVDC
<b>Input Voltage Signal Range</b>	0-20 VAC 0-200 VAC 0-600 VAC +/-20 VDC +/-200VDC +/- 600 VDC
<b>Operating Voltage</b>	20 to 265 VAC/11 to 265 VDC
<b>Loop Powered</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>