

DPM2-P-HL Cut Sheet



ProSense digital panel meter, panel mount, 1/8 DIN, 14mm
4-digit red LED, pulse or frequency input,
20-265 VAC/11-265 VDC operating voltage.

For complete product information, please see this item on our
store at the following link:



<https://www.automationdirect.com/pn/DPM2-P-HL>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14mm 4-digit red LED
Input	Pulse or frequency
Input Pulse/Frequency Signal Type	NPN, PNP, contact, encoder, magnetic pickup, NAMUR, AC voltage frequency
Operating Voltage	20-265 VAC/11-265 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM2-P-HL.pdf>
See store item page for other formats.