

# DPM3-AT-A-L Cut Sheet



ProSense digital panel meter, 1/8 DIN, 14mm 5-digit tri-color (red, green, amber) LED, analog, RTD or thermocouple input, 4-20 mA output, 22 to 53 VAC/10.5 to 70 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-AT-A-L>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Digital panel meter
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	1/8 DIN
<b>Display Type</b>	14mm 5-digit tri-color (red, green, amber) LED
<b>Input Current Signal Range</b>	+/-20mA
<b>Input Voltage Signal Range</b>	+/-10VDC +/-150mVDC +/-30mVDC +/-15mVDC
<b>Input Thermocouple Signal Type</b>	J, K, T, N
<b>Input RTD Signal Types</b>	Pt100
<b>Output</b>	4-20 mA
<b>Operating Voltage</b>	22 to 53 VAC/10.5 to 70 VDC
<b>Loop Powered</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>