

DPM3-AT-A2R-H Cut Sheet



ProSense digital panel meter, panel mount, 1/8 DIN, 14mm 5-digit tri-color (red, green, amber) LED, analog, load cell, RTD or thermocouple input, 4-20 mA, (2) 8A SPDT relays output, 85-265 VAC/100-300 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-AT-A2R-H>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14mm 5-digit tri-color (red, green, amber) LED
Input	Analog, load cell, RTD or thermocouple
Input Current Signal Range	+/- 20 mA
Input Voltage Signal Range	+/- 10 VDC

Input Thermocouple Signal Type	J, K, T, N
Input RTD Signal Types	Pt100
Input Load Cell Signal Range	+/- 15 mVDC, +/- 30 mVDC and +/- 150 mVDC
Output	4-20 mA, (2) 8A SPDT relays
Operating Voltage	85-265 VAC/100-300 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM3-AT-A2R-H.pdf>
See store item page for other formats.