

DPM3-E-H Cut Sheet



ProSense digital panel meter, 1/8 DIN, 14mm 5-digit tri-color (red, green, amber) LED, True RMS AC/DC current or voltage input, 85 to 265 VAC/100 to 300 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-E-H>

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14mm 5-digit tri-color (red, green, amber) LED
Input Current Signal Range	0-200mA AC True RMS 0-1A AC True RMS 0-5A AC True RMS shunt 0-50 mVAC True RMS shunt 0-60 mVAC True RMS shunt 0-100 mVAC True RMS +/-200mA DC +/-1A DC +/-5A DC shunt +/-50 mVDC shunt +/-60 mVDC shunt +/-100 mVDC
Input Voltage Signal Range	0-2 VAC True RMS 0-20 VAC True RMS 0-200 VAC True RMS 0-600 VAC True RMS +/-2 VDC +/-20 VDC +/-200 VDC +/-600 VDC
Operating Voltage	85 to 265 VAC/100 to 300 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document