

DPM3-E-L Cut Sheet



ProSense digital panel meter, panel mount, 1/8 DIN, 14mm 5-digit tri-color (red, green, amber) LED, True RMS AC/DC current or voltage input, 22-53 VAC/10.5-70 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-E-L>

Technical Specifications

| | |
|-----------------------------------|---|
| Brand | ProSense |
| Item | Digital panel meter |
| Mounting | Panel |
| Mounting Hole Size | 1/8 DIN |
| Display Type | 14mm 5-digit tri-color (red, green, amber) LED |
| Input | True RMS AC/DC current or voltage |
| Input Current Signal Range | <ul style="list-style-type: none">• 0-200 mA AC True RMS• 0-1A AC True RMS• 0-5A AC True RMS• shunt 0-50 mVAC True RMS• shunt 0-60 mVAC True RMS• shunt 0-100 mVAC True RMS• +/- 200 mA DC• +/- 1A DC• +/- 5A DC• shunt +/- 50 mVDC• shunt +/- 60 mVDC• shunt +/- 100 mVDC |

| | |
|-----------------------------------|---|
| Input Voltage Signal Range | <ul style="list-style-type: none">• 0-2 VAC True RMS• 0-20 VAC True RMS• 0-200 VAC True RMS• 0-600 VAC True RMS• +/- 2 VDC• +/- 20 VDC• +/- 200 VDC• +/- 600 VDC |
| Operating Voltage | 22-53 VAC/10.5-70 VDC |
| Loop Powered | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM3-E-L.pdf>
See store item page for other formats.