

# DPM3-P-A2R-H Cut Sheet



ProSense digital panel meter, 1/8 DIN, 14mm 5-digit tri-color (red, green, amber) LED, pulse and frequency input, 4-20 mA, (2) 8A SPDT relays output, 85 to 265 VAC/100 to 300 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-P-A2R-H>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Digital panel meter
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	1/8 DIN
<b>Display Type</b>	14mm 5-digit tri-color (red, green, amber) LED
<b>Input Pulse/Frequency Signal Type</b>	NPN, PNP, contact, encoder, magnetic pickup, NAMUR, AC voltage frequency
<b>Output</b>	4-20 mA, (2) 8A SPDT relays
<b>Operating Voltage</b>	85 to 265 VAC/100 to 300 VDC
<b>Loop Powered</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DPM3-P-A2R-H.pdf>  
See store item page for other formats.