

DPM3-P-H Cut Sheet



ProSense digital panel meter, panel mount, 1/8 DIN, 14mm 5-digit tri-color (red, green, amber) LED, pulse or frequency input, 85-265 VAC/100-300 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPM3-P-H>

Technical Specifications

| | |
|-----------------------------------|--|
| Brand | ProSense |
| Item | Digital panel meter |
| Mounting | Panel |
| Mounting Hole Size | 1/8 DIN |
| Display Type | 14mm 5-digit tri-color (red, green, amber) LED |
| Input | Pulse or frequency |
| Input Pulse/Frequency Signal Type | NPN, PNP, contact, encoder, magnetic pickup, NAMUR, AC voltage frequency |
| Operating Voltage | 85-265 VAC/100-300 VDC |
| Loop Powered | No |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DPM3-P-H.pdf>
See store item page for other formats.