

DPTA-20-10 Cut Sheet



ProSense air differential pressure transmitter, 0 to 10.0in of water column range, 4-20 mA analog output, 1/4in brass barbed process connection, 12 to 36 VDC operating voltage, screw terminals, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPTA-20-10>

Technical Specifications

Brand	ProSense
Item	Differential pressure transmitter
Media Type	Air and gases
Pressure Range	0 to 10.0in of water column
Analog Output	4-20 mA
Process Connection	1/4in brass barbed
Operating Voltage	12 to 36 VDC
Electrical Connection	Screw terminals
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document