

# DPTA-20-P5 Cut Sheet



ProSense air differential pressure transmitter, 0 to 0.5in of water column range, 4-20 mA analog output, 1/4in brass barbed process connection, 12 to 36 VDC operating voltage, screw terminals, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPTA-20-P5>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Differential pressure transmitter
<b>Media Type</b>	Air and gases
<b>Pressure Range</b>	0 to 0.5in of water column
<b>Analog Output</b>	4-20 mA
<b>Process Connection</b>	1/4in brass barbed
<b>Operating Voltage</b>	12 to 36 VDC
<b>Electrical Connection</b>	Screw terminals
<b>Mounting</b>	35mm DIN rail or panel

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DPTA-20-P5.pdf>  
See store item page for other formats.