

# DPTW-40 Cut Sheet



ProSense differential pressure transmitter, 0 to 40in of water column range, 4-20 mA analog output, 1/4in female NPT process connection, 12-32 VDC operating voltage, screw terminals, panel or wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPTW-40>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Differential pressure transmitter
<b>Media Type</b>	Air, water, gases, steam and liquid
<b>Pressure Range</b>	0 to 40in of water column
<b>Analog Output</b>	4-20 mA
<b>Process Connection</b>	1/4in female NPT
<b>Operating Voltage</b>	12-32 VDC
<b>Electrical Connection</b>	Screw terminals
<b>Mounting</b>	Panel or wall
<b>Includes</b>	Cable gland, panel/wall mounting bracket and hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DPTW-40.pdf>  
See store item page for other formats.