

DPTW-4 Cut Sheet



ProSense differential pressure transmitter, 0 to 4in of water column range, 4-20 mA analog output, 1/4in female NPT process connection, 12-32 VDC operating voltage, screw terminals, panel or wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DPTW-4>

Technical Specifications

Brand	ProSense
Item	Differential pressure transmitter
Media Type	Air, water, gases, steam and liquid
Pressure Range	0 to 4in of water column
Analog Output	4-20 mA
Process Connection	1/4in female NPT
Operating Voltage	12-32 VDC
Electrical Connection	Screw terminals
Mounting	Panel or wall
Includes	Cable gland, panel/wall mounting bracket and hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document