

DR-126 Cut Sheet



NITRA precision pneumatic regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 0.5-25 psi adjustable range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR-126>

Technical Specifications

Brand	NITRA
Item	Regulator
Regulator Type	Precision
Working Fluid	Air or inert gas
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Pressure Range	0.5-25 psi adjustable
Includes	Adjustment knob

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DR-126.pdf>
See store item page for other formats.