

# DR-133 Cut Sheet



NITRA precision pneumatic regulator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 2-120 psi adjustable range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR-133>

---

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Regulator
<b>Regulator Type</b>	Precision
<b>Working Fluid</b>	Pneumatic
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Pressure Range</b>	2-120 psi adjustable
<b>Includes</b>	Adjustment knob

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>