

DR10-AP-1A Cut Sheet



Micro Detectors inductive proximity sensor, rectangular, 10.3 x 28 x 16mm body, polyphthalamide housing, PNP, N.O. output, 3mm sensing distance, flush, 3 kHz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR10-AP-1A>

Technical Specifications

Brand	Micro Detectors	Sensing Distance	3mm
Item	Proximity sensor	Mounting Type	Flush
Sensor Type	Inductive	IO-Link Compatible	No
Application	Standard duty	Switching Frequency	3 kHz
Shape	Rectangular	Operating Voltage	10-30 VDC
Housing Size	10.3 x 28 x 16mm body	Operating Temperature	-25 to 75C
Housing Material	Polyphthalamide	Weld Field Immune	No
Sensing Method	Standard sensing	Chip Immune	No
Adjustable	No	IP Rating	IP67
Number of Wires	3	Connection	Pigtail
Switching Output	PNP	Conductor Size	24 AWG
Operation Mode	N.O. output	Cable Length	6.5ft/2m

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document