

# DR22B5-EB Cut Sheet



Fuji Electric audible alarm buzzer, 90 dB at 0.1m, 70 dB at 1m, 2.4 kHz to 3.3 kHz tone frequency, continuous/intermittent tone(s), 12-24 VAC/VDC, permanent LED indicator(s), red, 22mm, panel mount, plastic housing, black, IP00.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR22B5-EB>

## Technical Specifications

Brand	Fuji Electric
Item	Audible alarm buzzer
Loudness Decibel	90 dB at 0.1m, 70 dB at 1m
Tone Frequency	2.4 kHz to 3.3 kHz
Tone Type	Continuous/intermittent
Touch to Acknowledge	No
Number of Alarms	2
Voltage Rating	12-24 VAC/VDC

Indicator	Permanent LED
Light Color(s)	Red
Barrel Size	22mm
Mounting	Panel
Housing Material	Plastic
Color	Black
IP Rating	IP00

## Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DR22B5-EB.pdf>  
See store item page for other formats.