

DR22B5-HB Cut Sheet



Fuji Electric audible alarm buzzer, 90 dB at 0.1m, 70 dB at 1m, 2.4 kHz to 3.3 kHz tone frequency, continuous/intermittent tone(s), 100 to 110 VAC, permanent LED indicator(s), red, 22mm, panel mount, plastic housing, black, IP00.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR22B5-HB>

Technical Specifications

Brand	Fuji Electric
Item	Audible alarm buzzer
Loudness Decibel	90 dB at 0.1m, 70 dB at 1m
Tone Frequency	2.4 kHz to 3.3 kHz
Tone Type	Continuous/intermittent
Touch to Acknowledge	No
Voltage Rating	100 to 110 VAC
Indicator	Permanent LED
Light Color(s)	Red
Barrel Size	22mm
Mounting	Panel
Housing Material	Plastic
Color	Black
IP Rating	IP00

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DR22B5-HB.pdf>
See store item page for other formats.