

# DR30B5-EBZC Cut Sheet



Fuji Electric audible alarm buzzer, 90 dB at 0.1m, 70 dB at 1m, 2.4 kHz to 3.3 kHz tone frequency, continuous/intermittent tone(s), 12-24 VAC/VDC, permanent LED indicator(s), red, 30mm, panel mount, plastic housing, silver, IP00.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR30B5-EBZC>

## Technical Specifications

<b>Brand</b>	Fuji Electric
<b>Item</b>	Audible alarm buzzer
<b>Loudness Decibel</b>	90 dB at 0.1m, 70 dB at 1m
<b>Tone Frequency</b>	2.4 kHz to 3.3 kHz
<b>Tone Type</b>	Continuous/intermittent
<b>Touch to Acknowledge</b>	No
<b>Number of Alarms</b>	2
<b>Voltage Rating</b>	12-24 VAC/VDC

<b>Indicator</b>	Permanent LED
<b>Light Color(s)</b>	Red
<b>Barrel Size</b>	30mm
<b>Mounting</b>	Panel
<b>Housing Material</b>	Plastic
<b>Color</b>	Silver
<b>IP Rating</b>	IP00

## Agency Approvals

<b>UL Listed File #</b>	E44592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR20479
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DR30B5-EBZC.pdf>  
See store item page for other formats.