

DR30D0L-L9GZC Cut Sheet



Fuji Electric LED indicating light, permanent light function, 30mm, green, 41mm, dome, plastic base, metal bezel, 115-127 VAC, transformer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DR30D0L-L9GZC>

Technical Specifications

Brand	Fuji Electric
Item	Indicating light
Bulb Type	LED
Light Function	Permanent
IP Rating	IP65
Barrel Size	30mm
Contact Type	Operator only
Operator Color	Green

Light Color(s)	Green
Operator Size	41mm
Operator Shape	Dome
Base Material	Plastic
Bezel Material	Metal
Voltage Rating	115-127 VAC
Voltage Regulation	Transformer

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR20479
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DR30D0L-L9GZC.pdf>
See store item page for other formats.