

# DRF06 Cut Sheet



Roxburgh EMI input filter, 120/240 VAC, 1-phase, 6A, 35mm DIN rail mount, EMI/RFI filtering, 1-stage, general purpose, standard performance, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DRF06>

## Technical Specifications

<b>Brand</b>	Roxburgh
<b>Item</b>	Input filter
<b>Filter Type</b>	EMI
<b>Filter Voltage Rating</b>	120/240 VAC
<b>Number of Input Phases</b>	1
<b>Amperage Rating</b>	6A
<b>On/Off Switch</b>	No
<b>Fused</b>	No

<b>Mounting</b>	35mm DIN rail
<b>Filtering</b>	EMI/RFI
<b>Number of Filter Stages</b>	1
<b>SCCR Rating</b>	5kA SCCR
<b>Filter Application</b>	General purpose
<b>Filter Performance Level</b>	Standard performance
<b>Connector Type</b>	Screw terminals

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DRF06.pdf>  
See store item page for other formats.