

DS100806HW Cut Sheet



Stahlin Diamond Shield series enclosure, NEMA 1/3/3S/4X/12/13, 10 x 8 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DS100806HW>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	Diamond Shield
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3/3S/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	10 x 8 x 6in (HxWxD)
Enclosure Height	11.42in
Enclosure Width	9.79in
Enclosure Depth	6.31in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Crowned hinged screw cover
Hinge Type	Molded hinges with stainless steel pins
Number of Hinges Per Door	2
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DS100806HW.pdf>
See store item page for other formats.