

DSW181610HLL Cut Sheet



Stahlin Diamond Shield series enclosure, NEMA 1/3/3S/4X/12/13, 18 x 16 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned single-door, (2) twist-lock latches, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DSW181610HLL>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Stahlin |
| Item | Enclosure |
| Series | Diamond Shield |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/3/3S/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 18 x 16 x 10in (HxWxD) |
| Enclosure Height | 19.77in |
| Enclosure Width | 18.15in |
| Enclosure Depth | 10.34in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | Gray |
| Cover Type | Crowned single-door |
| Hinge Type | Molded hinges with stainless steel pins |
| Number of Hinges Per Door | 2 |
| Latch Type | (2) twist-lock latches |
| Padlock Attachment Type | Padlock hasp and staple |
| Window Material | SAR acrylic |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | | |
|-----------------------------|--|---------|
| UL Listed File # | E64358 | E362920 |
| UL Recognized File # | E333478 | |
| UL Hazardous File # | None | |
| CE | View CE declarations | |
| CSA File # | LR069014 | |
| RoHS Status | Yes (See CE Doc) | |
| EU REACH | View EU REACH document | |