

DVD-2AC4A-24A Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., brass body, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), Cv=2.45, 24 VAC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVD-2AC4A-24A>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air, oil, inert gas, water or emulsion
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Brass

Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Manual Override Type	Momentary
Flow Coefficient	2.45
Operating Voltage	24 VAC
Electrical Connection	18mm DIN style wiring plug
Form Factor	Standard
Includes	Viton seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DVD-2AC4A-24A.pdf>
See store item page for other formats.